Foam Cleaning Equipment Injector Mobile LP 3-10 II

Low Pressure

Item no.: 88659



3-10 Bar



Purpose and use.

The Injector Mobile LP 3-10 II is an injector with double inlet, mounted on a wide trolley for two drums. The design is compact and for easy use and service. It is for sites that require cleaning by Foaming and Disinfection.

The trolley is made in stainless steel and has room for hose, accessories etc.

The injector is capable of producing dry dense foam and by adjusting the air pressure, more wet dense foam.

The Injector Mobile LP 3-10 II is manual operated by valves, which is easy to operate.

All materials that is in contact with the product, is corrosion resistant.

Features / benefits.

Functions: Cleaning with Flush / Foam / Disinfection

Operator friendly: Easy understanding of the functions

Variable foam density: Capable of producing dry dense foam

Capable of producing wet dense foam

Adjusting product conc.: Easy change of concentration by changing

the colour coded orifice nozzle

Few installation requirements: No electricity required





Injector Mobile LP 3-10 II

Item no.: 88659

General Description

The Injector works like a hydraulic foam cabinet, (the Injector is essentially a "static pump"). Injectors work on the principle of a pressure differential: A vacuum is created which pulls "or pumps" the product into the mixing chamber. As standard, a non-return valve in the water inlet is mounted.

The trolley has mounted wheels without rubbing off affect. Furthermore, an outlet hose and a set of tubes are included.

Ordering Information

Shipping: All correspondence concerning shipping, should be directed: Mrs. Lene Wittendorf

Placing Orders and Enquiries:

All orders are acknowledged by fax, unless other special arrangements have been made.

All correspondence concerning new orders or progressing existing orders, should be directed to:

Mr. Anders S. Christensen Mrs. Lene Wittendorf

Technical enquiries:

Enquiries relating to product performance should be directed to:

Mr. Aksel A. Utoft

Mr. Anders S. Christensen

ScanFoam® Cleaning Equipment ApS.Telephone:+4586 57 25 99Niels Bohrs Vej 29b, StillingFax:+4586 57 20 86

8660 Skanderborg E-mail: anders.christensen@scanfoam.com

Denmark lene.wittendorf@scanfoam.com

Specifications

Water inlet: Connection: 1/2" hose nipple

Limitation: Min. feed pressure 3 bar

Max. feed pressure 10 bar Max. temperature 55 °C

Water consumption at 25 bar & 10 m 1/2" hose:

Flushing nominal 18 I/min
Foaming 6 I/min
Disinfecting 7 I/min

Air inlet: Connection 1/4" hose nipple

Limitation: Min. feed pressure 6 bar

Max. feed pressure 10 bar Air consumption at 6 bar 150 l/min

Prod. inlet: Connection: 2 suction tube

Dosing range 1-6%

Outlet: Connection: 3/4" hose nipple


Max length hose 3/4" 10 meters

Weight: 24 kg

Room for drums (Width x Depth) 53cm x 32cm

Included accessories:

Hose 3/4" 10 meter with ball valve, Foam tube, Flushing tube. Brackets for hose and the cleaning nozzles.



Low Pressure Injector Mobile LP 3-10 II Item no.: 88659 A. Utoft 2011-02a